MOBILE DRESSING SPINDLE

Dressing tools








For machines without rotating dressing device
Wide speed range
Speed detection with readjustment
Left & right rotation
Easy to use
Quick installation


MOBILE DRESSING SPINDLE











Mobile dressing system for any machine One system - 3 components

A fixed dressing system is not always required. Universally applicable and mobile systems are the better way for many users - especially for smaller companies. For this purpose we have developed the perfect solution: KREBSDRESS is a mobile dressing spindle system that can easily be used on any machines without rotating dressing technology. In the same way, it can also be installed in new machine systems. With KREBSDRESS ceramic bonded CBN and diamond grinding wheels can be dressed and conditioned. The spindle is equipped with a mounting plate for easy and quick installation.

The system offers ideal adaptation possibilities to the respective dressing situation. These include a wide speed range, actual speed detection with readjustment, selection of right and left rotation, and the possibility of very simply designed integration into the machine control system. In order to be able to achieve the workpiece qualities required today, a very high concentricity and sturdiness of the dressing spindle is required, which is ensured by a sophisticated design as well as high-precision and maintenance-free bearings Made in Germany.

1.500 - 15.000 U/min.
230V / 50-60Hz
ca. 1,7A
ca. 300 watts
20 Ncm
oilproof, 7m
Ø 6 mm
1,5 - 3 bar
yes
Precision spindle bearing
294 x 185 x 57 mm
215 x 100 x 115 mm
1,0 kg
4,9 kg







KREBSDRESS







The dressing spindle - Heart of the system

The spindle is the most important component in the dressing system. It is about the size of an envelope and can therefore be used flexibly and universally. In order to guarantee precise work and a long service life, the spindle is supplied with sealing air to protect it from moisture and dirt and cools the spindle. The exact dimensions and technical data of the spindle can be seen in the drawings and table overleaf/on the next page. Not designed for continuous operation. Recommendation: Use with sealing air! Sealing air hose is not included in the scope of delivery.

The control unit - Modern control center

The control unit is equipped with a sensitive touch screen for easy handling. Like the spindle, the control unit is also ultra-compact: it's just about the size of a sheet of paper, and the height is less than 6 cm. The entire system is always ready for use no matter where it is needed. The complete system will be delivered in a padded portable case for protection. All technical data is listed in the table overleaf/on the next page.

The dressing tool For most common dressing applications

The dressing spindle can be equipped with different dressing tools. With type FD85, a dressing wheel is already included that covers the most common dressing applications. For special applications, we also offer individually manufactured dressing tools. Ask us about it!

Scope of delivery

- Dressing spindle 300AS
- Operating terminal BT-01
- Dressing tool type FD85
- Cold appliance plug 230 V AC
- Screw plug 7-pin
- Sub-D, 9-pin cable
- Stable transport case

KREBS & RIEDEL
Schleifscheibenfabrik GmbH & Co. KG
Bremer Straße 44 • 34385 Bad Karlshafen
Tel.: +49 5672 184-0 • Fax: +49 5672 184-218
mail@krebs-riedel.de • www.krebs-riedel.de